

SBPR Series

Subatmospheric Back Pressure Regulators

Introduction

The SBPR Series subatmospheric back pressure regulator is designed to provide precise upstream vacuum control. One example of this could be to introduce a sample gas at a positive pressure into a vacuum chamber. Downstream from this chamber would be the SBPR and a vacuum pump. The positive pressure will build up in the chamber causing the SBPR to open and allow the chamber to return to the vacuum desired. The SBPR will then close and the process will repeat. The large diameter diaphragm aided by a vacuum assist spring, provides the user with optimum sensitivity for subatmospheric pressure control.



pressure regulators

Typical Applications

- Analytical instrumentation
- Gas and liquid sampling
- Research labs

Technical Data

CONSTRUCTION	316L stainless steel or brass (standard) MONEL® and HASTELLOY® C-276 (optional)
ADJUSTABLE PRESSURE CONTROL RANGES	1–30 psia (–27.7 in. H ₂ O to 15.3 psig)
OPERATING TEMPERATURE	–40° F to +300° F (–40° C to +148° C)
C_v COEFFICIENT	0.2
INLET/OUTLET CONNECTIONS	¼" FNPT

Features & Benefits

- Subatmospheric or positive back pressure control
- Large diaphragm for sensitive pressure control

Options

- Extra ports
- Panel mount (requires a 1³/₈" mounting hole)
- Pressure gauges
- Smaller orifice sizes available: 0.005, 0.03

Subatmospheric Back Pressure Regulators

Maximum Temperature and Control Pressures

SEAT MATERIAL	MAXIMUM TEMPERATURE	@	MAXIMUM CONTROL RANGE
Viton®	250° F (121° C)	@	1–30 psia
Kalrez®	300° F (148° C)	@	1–30 psia
PTFE	200° F (93° C)	@	1–30 psia

Temperatures in excess of 175° F (80° C) require the use of a T-handle or the tamper proof option.

To Order, contact your local Distributor Link below:

www.goreg.com/distributor/index.htm

Verify that your chosen part number is valid using the GO Wizards at

www.goreg.com/products/matrix/index.htm

How to Order

For additional configurations, consult the factory. **Standard items in bold.**

SBPR – 1 A 1 1 I 5 A 1 1 1 A

Body Material

- 1 316L stainless steel, stainless steel diaphragm
- 2 Brass, stainless steel diaphragm
- 4 MONEL®, INCONEL® diaphragm
- 6 HASTELLOY® C-276, INCONEL® diaphragm
- C 316L stainless steel, INCONEL® diaphragm, standard**

Port Configuration

- A Standard (body “A”)**
See pg. 28 for port locations.

Process Port Types

- 1 **¼” FNPT (¼” FNPT gauge ports)**
- 4 ⅜” FNPT (¼” FNPT gauge ports)
- 5 ½” FNPT (¼” FNPT gauge ports)

Cavity Finish

- 1 **< 25 Ra**

Actuator Material

- D Viton®
- I **PTFE**
- K Kalrez®

Options

- A** EB33 (oxygen cleaning)
- B** EB5 cleaning
- D** Helium leak test
- E** Pressure test certificate
- F** Certificate of Conformity
- G** CMTR

Cap Assembly

- 1 Standard, stainless steel**
- 2 T-handle, stainless steel
- 3 T-handle, panel mount, stainless steel
- 4 Panel mount, stainless steel
- 7 Captured vent, stainless steel
- 8 Tamper-proof, stainless steel
- 9 Fine adjust, ½” panel mount, stainless steel
- 0 Fine adjust, 1⅜” panel mount, stainless steel
- C** Captured vent, panel mount, stainless steel
- E** Tamper-proof, panel mount, stainless steel
- H** ¼” NPT dome loaded, stainless steel

Diaphragm Facing/Backing Material

- 1 PTFE / metal backing, standard**
- 2 PTFE / Viton®

Diaphragm Type

- 1 Standard diaphragm**

Control Range

- A 1–30 psia**

Flow Coefficient (Cv)

- 1 0.03
- 5 0.2**
- I 0.005

NOTE: Contact the factory for any additional requirements.

For flow curve charts, visit www.goreg.com.

Subatmospheric Back Pressure Regulators

Outline and Mounting Dimensions

